



BDALHC26350, Power Distribution Block Adder

By Burndy
Catalog # [BDALHC26350](#)

Highly Conductive Al Distribution Block, 620 Amp/Pole, #6 AWG- 350 kcmil (Run), #14-2/0 AWG (Tap)



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350
Number Of Poles	Adder
Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0

	• 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	12-2/0
Conductor - AL Str Tap	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Str Tap Range	14-2/0
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0

Current

Amperage Rating	620 A
Rating - Minimum Voltage	600

Dimensions

Package Height	4.250 in
Dimension - Height mm	90.2 mm
Dimension - Height inch	3.55 in
Package Weight	7.190 lb.
Dimension - Width mm	66 mm
Dimension - Width inch	2.58 in
Package Length	18.250 in
Package Width	6.100 in

Dimension - L Length Overall mm	145 mm	UPC 14 Digit GTIN	00781810645611
Dimension - Length Overall inch	5.70 in	Logistics	
General		Minimum Pack Quantity	1
		Pallet Quantity	648
		Carton Quantity	18
		Operational	
		Temperature Rating	194° F
		Product Assets	
Plated	N	Catalog [English]	
Trade Name	VERSIPOLE™		
UPC	781810645611		
Insulation	Y		
Material	Aluminum		
Plating Type	Tin		
UPC 12 Digit	781810645611		



A Hubbell brand