

CLAMPING SQUARES

RIGHT ANGLE BRACKETS

These precision machined angle squares hold material at 90°. The holes and slots combination allow for infinite adjustments in fixturing. For heavy duty applications, see the Riser Blocks on *pg. 48*.



| Part No. | Dimension (in) | Plate Thickness (in) | Holes | Slot Length (in) | Weight (lb) |
|----------|------------------|----------------------|-------|------------------|-------------|
| T50304 | 1.6 x 3.6 x 1.18 | 0.47 | 1 | 2.6 | 0.5 |
| T50305 | 3.6 x 3.6 x 1.18 | | 3 | 2.6 | 0.7 |
| T50310 | 3.6 x 6 x 1.18 | | 3 | 5.0 | 1.0 |
| T50330 | 12 x 6 x 2 | | 11 | 5.0 | 4.5 |

ECONO STOP & CLAMPING SQUARES *

Economy Stop and Clamping Squares feature three surfaces for use in a wide variety of fit up applications.

Place Inserta Pliers or Inserta Clamps into any of the CNC machined holes for horizontal or vertical clamping at any height. Stack the Clamping Squares to brace tall workpieces. Use the top holes for mounting the Squares in a fixed location. The lower base is slotted for adjustable mounting.

Top and bottom plates are 0.47" thick and front sides are 0.12" thick.



| Part No. | Dimension (in) | Weight (lb) |
|----------|----------------|-------------|
| T50205 | 2 x 4.5 x 4 | 2.3 |
| T50210 | 2 x 5.5 x 8 | 3.1 |
| T50215 | 2 x 5.5 x 12 | 4.2 |

* The Econo Stop & Clamping Squares will be discontinued by the end of 2021 and only available while stock lasts.

