



BDAMHCEB, Power Distribution Block Plastic End Barrier

By Burndy
Catalog # [BDAMHCEB](#)

Plastic End Barrier for Medium Size VERSIPOLE™ Configurable
Power Distribution Blocks



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	4.800 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in
Package Weight	2.400 lb.
Dimension - Width mm	4 mm

Dimension - Width inch	0.14 in
Package Length	6.250 in
Package Width	4.900 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in

General

Plated	N
Trade Name	VERSIPOLE™
UPC	781810646281
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810646281
UPC 14 Digit GTIN	00781810646281

Logistics

Minimum Pack Quantity	1
Pallet Quantity	10800
Carton Quantity	600

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand