



1PBS250, UV Rated Black Splice/Reducer, 2-Port, 10-250 kcmil

By Burndy
Catalog # [1PBS250](#)

UV Rated Covering, Oxide inhibitor pre-installed. In-Line Splice Reducer.
#10 AWG-250 kcmil, 1 wire each end.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application


For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG



Conductor Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	53.3 mm
Dimension - Height inch	2.10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Width	1.19 in
Dimension - Width fraction	1-19/100 in
Dimension - Screw Size inch	5/8
Length	4.01 in
Dimension - Width mm	30 mm
Dimension - Width inch	1.19 in
Height	2.1 in
Dimension - Length Overall inch	4.01 in
Dimensions	4.01 in x 1.19 in x 2.1 in

Force Related

Installation Torque Recommended
in-lb275 in-lb

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810295915
Type	BIBS, Multi-Port
Hex Key	5/16
Material	Aluminum



A Hubbell brand

Plating Type	Unplated
UPC 12 Digit	781810295915
UPC 14 Digit GTIN	00781810295915

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3240
Carton Quantity	90

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)