



BDASHC112/01, Power Distribution Block Adder

By Burndy
Catalog # [BDASHC112/01](#)

Terminal Block, 3.08 in L, .93 in W, Glass Filled Polycarbonate, AWG 14 - 2/0 (Run), AWG 14 - 2/0 (Tap)

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - UL Recognized	No
Buy American Compliant	Under Review
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Run	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - AL Str Tap	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1 • 1/0



Conductor - Copper Str Run Range	• 2/0 14-2/0
Conductor - Copper Str Run	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Number Of Poles	Adder
Conductor - Copper Str Tap Range	14-2/0
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0

Current

Amperage Rating	175 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	71.4 mm
Dimension - Height inch	2.81 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm 78 mm
Dimension - Width mm 24 mm
Dimension - Width inch 0.93 in
Dimension - Length Overall inch 3.08 in

General

Trade Name VERSIPOLE™
Insulation Y
Plated N
Sub Brand VERSI-POLE
UPC 781810645475
Type BDA
Material Aluminum

Plating Type Tin
UPC 12 Digit 781810645475
UPC 14 Digit GTIN 00781810645475

Logistics

Minimum Pack Quantity 1
Pallet Quantity 5940
Carton Quantity 36

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand