



BDASHCEB, Power Distribution Block Plastic End Barrier

By Burndy
Catalog # [BDASHCEB](#)

Plastic End Barrier for Small Size VERSIPOLE™ Configurable
Power Distribution Blocks



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	1.750 in
Dimension - Height mm	71.4 mm
Dimension - Height inch	2.81 in
Package Weight	1.010 lb.
Dimension - Width mm	3 mm

Dimension - Width inch	0.12 in
Package Length	9.500 in
Package Width	4.250 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in

General

Plated	N
Trade Name	VERSIPOLE™
UPC	781810646298
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810646298
UPC 14 Digit GTIN	00781810646298

Logistics

Minimum Pack Quantity	1
Pallet Quantity	34200
Carton Quantity	600

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)