



38CHENBOX100, 3/8" Hex Nut, Silicon Bronze

By Burndy  
Catalog # 38CHENBOX100

Silicon Bronze NUT ,3/8-16 Stud ,Thread series-Class 2B.

Features

- DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

Configuration

|                |     |
|----------------|-----|
| Connector Type | Nut |
|----------------|-----|

Dimensions

|                                |           |
|--------------------------------|-----------|
| Package Height                 | 0.000 in  |
| Dimension - Bolt Size fraction | 3/8       |
| Package Weight                 | 0.000 lb. |
| Package Length                 | 0.000 in  |

|                                   |          |
|-----------------------------------|----------|
| Package Width                     | 0.000 in |
| Dimension - Outside Diameter inch | 0.56 in  |
| Width                             | 0.38 in  |
| Dimension - Thread Size           | 3/8-16   |
| Dimension - Threads per inch      | 16       |
| Dimension - Bolt Size inch        | 0.375 in |

Force Related

|                                       |            |
|---------------------------------------|------------|
| Installation Torque Recommended in-lb | 180 LBS/in |
|---------------------------------------|------------|

General

|                   |                |
|-------------------|----------------|
| UPC               | 781810376133   |
| Material          | Silicon Bronze |
| UPC 14 Digit GTIN | 00781810376133 |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Carton Quantity       | 1 |

Product Assets

[Catalog \[English\]](#)