



795454T, Shear Bolt WEJTAP™ Connector

By Burndy
Catalog # [795454T](#)



Main Conductor: 636 ACSR - 900 MCM (.973"-1.108") Tap
Conductor: #6 - #2 AAC (.162"-.292") Tin Plated

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench
- Installed overhead
- Meets or exceeds current carrying capacity of conductors being connected
- "Spring like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Corrosion resistant highly conductive copper and bronze alloys with a pure copper insert between conductors increases conductivity and lower electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration where outside crews might not have Shoot-On or compression tooling

General

Catalog Number	795454T
UPC	621945674325

Conductor Related

Conductor Range	Main Conductor: 363 ACSR-900 kcmil, Tap: #6-#2 AAC
-----------------	--

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Installation Manuals - Tap Connector Installation Instructions](#)
[Specifications - 795454T](#)
[Video - WEJTAP™ Installation with Gloves](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-795454T-SPEC-EN | REV 7/2025