




BDBLCS10LR3DW, Large Flex Rated Lay-in Style Pwr Dist Block

By Burndy
Catalog # [BDBLCS10LR3DW](#)



BURNDY® VERSIPOLE™ Lay-in Distribution blocks

Features

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing
- Double-Wide Series include Covers

Conductor

Conductor - Copper DLO Size Range	Run - 777 Kcmil, Tap - # 6 Awg - 4/0 Str.
Conductor - Copper Flex H Run Range	500-750 Flex
Conductor - Copper Str Run	500-750 Kcmil
Conductor - Copper Flex K Tap Range	# 6 Awg - 4/0 Str. Flex
Number Of Poles	3
Conductor - Copper Flex H Tap Range	# 6 Awg - 4/0 Str. Flex
Conductor - Copper Flex I Run Range	500-750 Flex
Conductor - Copper Str Tap	# 6 Awg - 4/0 Str.
Conductor - Copper Flex I Tap Range	# 6 Awg - 4/0 Str. Flex
Conductor - Copper Flex K Run Range	500-750 Flex

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Current

Amperage Rating	475
Voltage Rating	600 V

Dimensions

Package Height	0.000 in
Length	17.84 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	4.1 in

General

UPC	621945553620
Material - Mounting Hardware	Stainless steel
Material Type - Screw	Tin plated Aluminum
Item Type	M
Material	Aluminum
Material - Base	NYLON 6/6
UPC 12 Digit	621945553620

Logistics

Pallet Quantity	84
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)