



ASA800U, Terminal Stacking Adapter, Al/Cu, 2-Slot, 800 kcmil

By Burndy
Catalog # ASA800U

Used with standard NEMA 2- or 4-Hole terminals; to stack 4-Hole terminations, two stacking adapters are needed assembled side-by-side, AL/CU, 800 kcmil

Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adapters assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

Application


For Aluminum And Copper Terminals

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
-------------------------	---



Conductor - AL Str Size Range	• 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - Copper Str Size	1/0 AWG-800 kcmil • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	1/0 -800 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in
Dimension - Height mm	28.7 mm
Dimension - Height inch	1.13 in
Dimension - Height fraction	1-1/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	20 mm

Width	1 in	Sub Brand	HYSTACK
Length	3 in	UPC	781810521021
Height	1.13 in	Type	Stacking Adapters
Dimension - Bolt Size inch	3.50 in	Material	Aluminum
Dimension - Length Overall inch	0.78 in	Plating Type	Tin
Dimensions	3 in x 1 in x 1.13 in	UPC 12 Digit	781810521021
		UPC 14 Digit GTIN	00781810521021
Force Related		Logistics	
Installation Torque	480 LBS/in	Pallet Quantity	4640
Recommended in-lb		Carton Quantity	10
General		Operational	
Trade Name	HYSTACK™	Temperature Rating	194° F
Material - Hardware	DURIUM™ Silicon Bronze		
Physical Attribute - Screw Type	Hexagonal Bolt		
Plated	Y	Product Assets	
		Catalog [English]	



A Hubbell brand