



BA10E10M, Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # [BA10E10M](#)



Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.36 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#10
Length	1 in
Dimension - Z inch	0.26 in
Height	0.37 in
Width	0.37 in
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.00 in
Dimension - Stud Size inch	#10
Dimensions	1 in x 0.37 in x 0.37 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Ring
UPC	781810028865
Type	Ring Tongue
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810028865
UPC 14 Digit GTIN	00781810028865

Product Assets

[Catalog \[English\]](#)