

BA10EL8, Vinyl Locking Fork Terminal, 12-10 AWG, #8 Stud

By Burndy
Catalog # [BA10EL8](#)

Vinyl Insulated Copper Locking Fork Terminal For 12 - 10 AWG, #8 Stud,
Bulk Packaged



Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.32 in
Dimension - Hole Size inch	0.17 in
Dimension - Stud Size inch	#8
Dimension - Bolt Size fraction	#8
Length	1.07 in
Dimension - Z inch	0.26 in
Height	0.32 in
Dimension - Length Overall inch	1.07 in
Dimensions	1.07 in x 0.32 in x 0.32 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810026892
Type	BA-EL, Locking
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026892
UPC 14 Digit GTIN	00781810026892

Logistics

Minimum Pack Quantity	500
Pallet Quantity	99999
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)