



BA14E10, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14E10](#)

Vinyl Ring Terminal For 16 - 14 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU-C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Z inch	0.26 in
Dimension - Pad Width inch	0.31 in
Length	0.85 in
Dimension - Hole Size fraction	1/5 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	#10
Dimension - Length Overall inch	0.85 in
Width	0.32 in
Height	0.32 in
Dimensions	0.85 in x 0.32 in x 0.32 in

General

Sub Brand	VINYLUG
Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
Type	Ring Tongue
Material	Copper
Plating Type	Tin - Electroplated
UPC	781810026625

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)