



BDBLCS5S5S3, Flex Rated Stud Style Power Distribution Block

By Burndy
Catalog # [BDBLCS5S5S3](#)

Distribution Block, 3-Pole, Stud-to-Stud, Run: 1/2" Stud, Tap: 1/2"
Stud, 620 Amp Rating

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications

Certification - CSA Approved	No
Certification - cULus	Yes
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	




Image represents single pole

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Dimensions

Weight	1.53 lb.
--------	----------

General

Material	Aluminum
UPC	621945518896
Trade Name	VERSIPOLE™

Logistics

Minimum Pack Quantity	1
Carton Quantity	2
Pallet Quantity	144

Product Assets

[Catalog \[English\]](#)