



Image represents single pole



BDBLCS5SA1, 1-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBLCS5SA1](#)

Box-to-Stud 1-12 1/2-4

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications

Certification - cULus	Yes
Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	---

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Height mm	0 mm
Length	9.09 in
Height	5.54 in

General

Trade Name	VERSIPOLE™
Plated	Y
Insulation	Y
UPC 12 Digit	781810675915
UPC 14 Digit GTIN	007818106759155
Material	Aluminum
Plating Type	Tin
UPC	621945481725

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	720

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)