



BA14E516, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14E516](#)

Vinyl Ring Terminal For 16 - 14 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	16 AWG 15 AWG 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	16 AWG 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Z inch	0.45 in
Dimension - Pad Width inch	0.53 in
Length	1.15 in
Dimension - Hole Size fraction	8/25 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.32 in
Dimension - Stud Size inch	5/16 in
Dimension - Length Overall inch	1.15 in
Width	0.54 in
Height	0.54 in
Dimensions	1.15 in x 0.54 in x 0.54 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
Type	Ring Tongue
Material	Copper
Plating Type	Tin - Electroplated
UPC	781810082195

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)