



BA16EL6M, Terminal Vinyl Insulated Locking Fork #16 AWG #6 Stud on Mylar Reel

By Burndy
Catalog # [BA16EL6M](#)

BURNDY; VINYLUG; Terminal fork; RoHS Compatible; Wire Size: #22-16 AWG; Material: Copper; Color: Red

Features

- Vinyl Locking Fork Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - RoHS Compliance Status	CM
Certification - cULus	N
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size	• 20 • 18 AWG • 17 AWG • 16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal



Dimensions

Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Dimension - Bolt Size fraction	#6
Length	0.87 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.23 in
Height	0.29 in
Width	0.29 in
Dimension - Thread Size	-
Dimension - Hole Size inch	0.14 in
Dimension - Length Overall inch	0.87 in
Dimension - Stud Size inch	#6
Dimensions	0.87 in x 0.29 in x 0.29 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG
Physical Attribute - Tongue Type	Locking Fork
UPC	781810029312
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810029312
UPC 14 Digit GTIN	00781810029312

Product Assets

[Catalog \[English\]](#)