



BDALHCEB, Power Distribution Block Plastic End Barrier

By Burndy
Catalog # [BDALHCEB](#)

Plastic End Barrier for Large Size VERSIPOLE™ Configurable
Power Distribution Blocks



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	5.400 in
Dimension - Height mm	90.2 mm
Dimension - Height inch	3.55 in
Package Weight	3.030 lb.
Dimension - Width mm	4 mm

Dimension - Width inch	0.15 in
Package Length	5.800 in
Package Width	3.600 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in

General

Plated	N
Trade Name	VERSIPOLE™
UPC	781810646205
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810646205
UPC 14 Digit GTIN	00781810646205

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8400
Carton Quantity	600

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)