



BDAMHC11350, Power Distribution Block Adder

By Burndy
Catalog # BDAMHC11350

Highly Conductive Al Distribution Block, 310 Amp/Pole, #6 AWG-350 kcmil Run/Tap



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350
Number Of Poles	Adder
Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0

	• 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	6-350
Conductor - AL Str Tap	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor - Copper Str Tap Range	6-350
Conductor - Copper Str Tap	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350

Current

Amperage Rating	310 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.
Dimension - Width mm	44 mm

Dimension - Width inch	1.72 in	Insulation	Y
Package Length	0.000 in	Material	Aluminum
Package Width	0.000 in	Plating Type	Tin
Dimension - L Length Overall mm	127 mm	UPC 12 Digit	781810646229
Dimension - Length Overall inch	5.00 in	UPC 14 Digit GTIN	00781810646229
Force Related		Logistics	
Installation Torque	275 in-lb	Pallet Quantity	2028
Recommended in-lb		Carton Quantity	6
General		Operational	
Plated	N	Temperature Rating	194° F
Trade Name	VERSIPOLE™	Product Assets	
UPC	781810646229	Catalog [English]	



A Hubbell brand