



BDAMHC14500, Power Distribution Block Adder

By Burndy  
Catalog # [BDAMHC14500](#)

BURNDY® VERSIPOLE™ Power Distribution Block



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | Yes |
| Certification - CSA Approved  | No  |

Conductor

|                                  |                                                                                                                                                                                                                                     |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Run Range | 4-500                                                                                                                                                                                                                               |
| Conductor - Copper Str Run       | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li><li>• 250</li><li>• 300</li><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul> |
| Number Of Poles                  | Adder                                                                                                                                                                                                                               |
| Conductor - AL Str Run Range     | 4-500                                                                                                                                                                                                                               |
| Conductor - AL Str Run           | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li></ul>                                                                                     |

|                                  |                                                                                                                                                                                                                        |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                  | <ul style="list-style-type: none"><li>• 250</li><li>• 266.8</li><li>• 300</li><li>• 336.4</li><li>• 350</li><li>• 397.5</li><li>• 400</li><li>• 450</li><li>• 477</li><li>• 500</li></ul>                              |
| Conductor - AL Str Tap Range     | 12-2/0                                                                                                                                                                                                                 |
| Conductor - AL Str Tap           | <ul style="list-style-type: none"><li>• 12</li><li>• 10</li><li>• 8</li><li>• 6</li><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul>                                                  |
| Conductor - Copper Str Tap Range | 14-2/0                                                                                                                                                                                                                 |
| Conductor - Copper Str Tap       | <ul style="list-style-type: none"><li>• 14</li><li>• 12</li><li>• 10</li><li>• 9</li><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul> |

Current

|                          |       |
|--------------------------|-------|
| Amperage Rating          | 380 A |
| Rating - Minimum Voltage | 600   |

Dimensions

|                         |          |
|-------------------------|----------|
| Package Height          | 0.000 in |
| Dimension - Height mm   | 82.6 mm  |
| Dimension - Height inch | 3.25 in  |

|                                 |           |
|---------------------------------|-----------|
| Package Weight                  | 0.000 lb. |
| Dimension - Width mm            | 44 mm     |
| Dimension - Width inch          | 1.72 in   |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 127 mm    |
| Dimension - Length Overall inch | 5.00 in   |

General

|            |              |
|------------|--------------|
| Plated     | N            |
| Trade Name | VERSIPOLE™   |
| UPC        | 781810646236 |
| Insulation | Y            |

|                   |                |
|-------------------|----------------|
| Material          | Aluminum       |
| Plating Type      | Tin            |
| UPC 12 Digit      | 781810646236   |
| UPC 14 Digit GTIN | 00781810646236 |

Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 1  |
| Pallet Quantity       | 1  |
| Carton Quantity       | 18 |

Operational

|                    |        |
|--------------------|--------|
| Temperature Rating | 194° F |
|--------------------|--------|

Product Assets

[Catalog \[English\]](#)



A Hubbell brand