



BDAMHC162500, Power Distribution Block Adder

By Burndy
Catalog # [BDAMHC162500](#)

Highly Conductive Al Distribution Block, 380 Amp/Pole, #4 AWG-500 kcmil Run, #14-#2 AWG Tap



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Run	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350 • 400 • 450 • 500
Number Of Poles	Adder
Conductor - AL Str Run Range	4-500
Conductor - AL Str Run	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0

Conductor - AL Str Tap Range	12-2
Conductor - AL Str Tap	• 12 • 10 • 8 • 6 • 4 • 3 • 2
Conductor - Copper Str Tap Range	14-2
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2

Current

Amperage Rating	380 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.
Dimension - Width mm	44 mm
Dimension - Width inch	1.72 in
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	127 mm	Material	Aluminum
Dimension - Length Overall inch	5.00 in	Plating Type	Tin
		UPC 12 Digit	781810646274
		UPC 14 Digit GTIN	00781810646274
Force Related		Logistics	
Installation Torque Recommended in-lb	500 in-lb	Pallet Quantity	1872
		Carton Quantity	6
General		Operational	
Plated	N	Temperature Rating	194° F
Trade Name	VERSIPOLE™		
UPC	781810646274		
Insulation	Y	Product Assets	
		Catalog [English]	



A Hubbell brand