




BDBLCS10LV1DW, Large Flex Rated Lay-in Style Pwr Dist Block

By Burndy
Catalog # [BDBLCS10LV1DW](#)

BURNDY® VERSIPOLE™ Lay-in Distribution blocks



Features

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing
- Double-Wide Series include Covers

Conductor

Conductor - Copper DLO Size Range	Run - 777 Kcmil, Tap - 535 Kcmil
Conductor - Copper Flex H Run Range	500-750 Flex
Conductor - Copper Str Run	500-750 Kcmil
Conductor - Copper Flex K Tap Range	# 4 Awg - 500 Kcmil Flex
Number Of Poles	1
Conductor - Copper Flex H Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex I Run Range	500-750 Flex
Conductor - Copper Str Tap	# 4 Awg - 500 Kcmil
Conductor - Copper Flex I Tap Range	# 4 Awg - 500 Kcmil Flex
Conductor - Copper Flex K Run Range	500-750 Flex

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Current

Amperage Rating	475
Voltage Rating	600 V

Dimensions

Package Height	0.000 in
Length	6.16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	4.1 in

General

UPC	621945550155
Material - Mounting Hardware	Stainless steel
Material Type - Screw	Tin plated Aluminum
Item Type	M
Material	Aluminum
Material - Base	NYLON 6/6
UPC 12 Digit	621945550155

Logistics

Pallet Quantity	216
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)