



BDBLHC223503, 3-Pole Power Distribution Block

By Burndy
Catalog # [BDBLHC223503](#)

Aluminum Power Distribution Block, 3 Pole, Run and Tap: #6
AWG - 350 kcmil, 620 Amp/Pole



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	6-350
Conductor - AL Str Tap	• 6 • 4 • 3 • 2 • 1 • 1/0

- 2/0
- 3/0
- 4/0
- 250
- 266.8
- 300
- 336.4
- 350

Conductor - Copper Str Run
Range

Conductor - Copper Str Run

6-350

- 6
- 5
- 4
- 3
- 2
- 1
- 1/0
- 2/0
- 3/0
- 4/0
- 250
- 300
- 350

Number Of Poles

Conductor Type

3

- AL C Str-Run
- CU C Str-Run
- AL C Str-Tap
- CU C Str-Tap

Conductor - Copper Str Tap
Range

Conductor - Copper Str Tap

6-350

- 6
- 5
- 4
- 3
- 2
- 1
- 1/0
- 2/0
- 3/0
- 4/0
- 250
- 300
- 350

Current

Amperage Rating

620 A

