



BDBLHC226003, 3-Pole Power Distribution Block

By Burndy
Catalog # BDBLHC226003

Aluminum Power Distribution Block, 3 Pole, Run and Tap: #2
AWG - 600 kcmil, 840 Amp/Pole

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	2-600
Conductor - Copper Str Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350 • 400 • 450 • 500 • 550 • 600
Number Of Poles	3
Conductor - AL Str Run Range	2-600
Conductor - AL Str Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8

Conductor - AL Str Tap Range	• 300 • 336.4 • 350 • 397.5 • 400 • 450 • 477 • 500 • 550 • 556.5 • 600
Conductor - AL Str Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400 • 450 • 477 • 500 • 550 • 556.5 • 600
Conductor - Copper Str Tap Range	2-600
Conductor - Copper Str Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350 • 400 • 450 • 500 • 550 • 556.5 • 600

Current

Amperage Rating	840 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	90.2 mm
Length	7.89 in
Dimension - Height inch	3.55
Package Weight	0.000 lb.
Dimension - Width mm	145 mm
Dimension - Width inch	5.70 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	200
Height	3.55 in
Width	4.75 in
Dimension - Length Overall inch	7.89
Dimensions	7.89 in x 4.75 in x 3.55 in



A Hubbell brand

General

Plated	N
Trade Name	VERSIPOLE™
UPC	781810652008
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810652008
UPC 14 Digit GTIN	00781810652008

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	6

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)