



BDBLHCCOVER, Power Distribution Block Cover

By Burndy
Catalog # [BDBLHCCOVER](#)

Large Size Cover for VERSIPOLE Distribution Block Only, Order 1 Cover per Pole



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	---

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	2.61 in
----------------------------	---------

Dimension - Height mm	22.1 mm
Length	5.7 in
Dimension - Height inch	0.87 in
Dimension - Width mm	66 mm
Dimension - Width inch	2.61 in
Dimension - L Length Overall mm	154 mm
Height	3.55 in
Width	4.75 in
Dimension - Length Overall inch	6.07 in
Dimensions	5.7 in x 4.75 in x 3.55 in

General

Plated	Y
Trade Name	VERSIPOLE™
Sub Brand	VERSI-POLE
UPC	781810646120
Type	BDB
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810646120
UPC 14 Digit GTIN	00781810646120

Logistics

Pallet Quantity	4400
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)