



BDBLCS4T2, 2-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBLCS4T2](#)

Distribution Block, 2-Pole, Run & Tap: #6 AWG-350 kcmil
(B,C,H,I,K, 373 DLO)

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications


Standards - RoHS Compliance Status	CM
Certification - cULus	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Number Of Poles	2
Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	6 AWG - 350 kcmil
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG - 350 kcmil

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------



Current

Amperage Rating	620 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	4.15
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	157
Dimension - Length Overall inch	6.17

General

Plated	Y
Trade Name	VERSIPOLE™
UPC	781810676035
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810676035
UPC 14 Digit GTIN	00781810676035

Logistics

Minimum Pack Quantity	1
Pallet Quantity	216
Carton Quantity	3

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)