



Image represents single pole



BDBLCS5S5S1, Flex Rated Stud Style Power Distribution Block

By Burndy
Catalog # [BDBLCS5S5S1](#)

Distribution Block, 1-Pole, Stud-to-Stud, Run: 1/2" Stud, Tap: 1/2"
Stud, 620 Amp Rating

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Dimensions

Height	5.54 in
Length	9.09 in

General

Material	Aluminum
UPC	621945481701

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	720

Product Assets

[Catalog \[English\]](#)