



BDBLCS7X1DW, Large Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBLCS7X1DW](#)

Double Wide Power Distribution Block, 1 Pole, Run & Tap: #4
AWG - 500 (B,C,H,I,K, 535 DLO)

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO
- Double-Wide Series boxes include covers


Application

The VERSIPOLE Configurable Series Power Distribution Blocks are used for splicing and distributing power from primary run(s) to secondary/branch circuits.

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
Buy America(n) Qualified	Contact Manufacturer

Image represents single pole



Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Current

Voltage Rating	1000 V
----------------	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Length	17.84 in
Height	5.54 in

General

Sub Brand	VERSIPOLE
Type	DISTRIBUTION BLOCK
Material	Aluminum
UPC	621945481626

Logistics

Minimum Pack Quantity	1
Carton Quantity	3
Pallet Quantity	216

Product Assets

[Catalog \[English\]](#)