



BDBLHC163503, 3-Pole Power Distribution Block

By Burndy
Catalog # [BDBLHC163503](#)

Aluminum Power Distribution Block, 3 Pole, Run: 6 AWG-350 kcmil, Tap: #14 - 2/0 AWG, 310 Amp/Pole



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	14-2/0
Conductor - AL Str Tap	• 4 • 3 • 2 • 1 • 1/0 • 2/0

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350
Number Of Poles	3
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	14-2/0
Conductor - Copper Str Tap	• 4 • 3 • 2 • 1 • 1/0 • 2/0

Current

Amperage Rating	310 A
Rating - Minimum Voltage	600

Dimensions

Package Height	4.250 in
Dimension - Height mm	90.2 mm
Dimension - Height inch	3.55
Package Weight	7.040 lb.
Package Length	18.250 in
Package Width	6.100 in
Dimension - L Length Overall mm	200
Width	4.75 in
Length	7.89 in
Dimension - Width mm	145 mm
Dimension - Width inch	5.70 in

Height	3.55 in
Dimension - Length Overall	7.89
inch	
Dimensions	7.89 in x 4.75 in x 3.55 in

General

Trade Name	VERSIPOLE™
Insulation	Y
Plated	Y
Sub Brand	VERSI-POLE
UPC	781810645857
Type	BDB
Material	Aluminum

Plating Type	Tin
UPC 12 Digit	781810645857
UPC 14 Digit GTIN	00781810645857

Logistics

Pallet Quantity	216
Carton Quantity	6

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand