



BIBS2/08FX, Flex, 8-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBS2/08FX](#)



Aluminum UNITAP, Single-Sided, #14 - 2/O Class B & C, #14 - #1 Class G,H,I,K, DLO, 8 Port

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	14 - 1 Str
Conductor Size	14-2/O AWG
Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Fex-Size
Conductor - Copper Str Size Range	14 AWG - 2/O AWG
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str

Configuration

Number Of Ports	8
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	35 mm
Dimension - Height inch	1.38 in
Package Weight	0.000 lb.
Dimension - Width mm	33 mm
Dimension - Width inch	1.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	134.37 mm
Dimension - Length Overall inch	5.298 in

General

Plated	Y
Color Code	Black
Trade Name	UNITAP™
UPC	621945439559
Insulation	Y
Material	Aluminum
Plating Type	Tin Plated Aluminum
UPC 12 Digit	621945439559
UPC 14 Digit GTIN	00621945439559

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)