



Image represents single pole



BDBMCS3SM2, Flex Rated Stud Style Power Distribution Block

By Burndy
Catalog # [BDBMCS3SM2](#)

Aluminum Power Distribution Block, 2 Pole, Run: 3/8" Stud, Tap: #14 - 2/0 AWG (B,C,H,I,K, DLO), 420 Amp/Pole

Features

- 600 Volt Rated
- Listed to UL1953
- Rated for use with code and flex conductor without requiring ferrules
- AL9CU dual rated for use with copper and aluminum conductors
- Range taking conductor ports can accommodate wire sizes up to 535 DLO and can support up to 5 run conductors and up to 24 tap conductors
- High Schort-Circuit Current Rating up to 100kA with proper fusing

Specifications

Certification - CSA Approved	No
Certification - cULus	Yes
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	

Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Dimensions

Weight	1.18 lb.
--------	----------

General

Material	Aluminum
UPC	621945518841
Trade Name	VERSIPOLE™

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)