



# BIPC50010SC, Ins. Piercing, Cu/Al, R: 3/0-500, T: #10-2

By Burndy  
Catalog # [BIPC50010SC](#)

Mechanical Insulation Piercing Connector, Cu/Al, Splicing, Tapping, and Dead-End Applications. Run: 3/0-500, Tap: #10-2

## Features

- Flexibility! One connector allows for tap, splice or dead-end configurations
- Time Savings! Requires no cable stripping, conductor brushing, inhibitor application or after installation taping
- Engineered shear bolt technology applies consistent torque for efficient and reliable connectors
- Easy installation and removal - only requires 6-point socket impact driver
- cULus Listed Splicing Wire Connector, AL9CU Rated, for copper and aluminum conductor combinations up to 90 degrees C, \*600 Volt applications
- Insulation piercing design for use in multiple applications - overhead covered and bare taps, service and metering connections, and lighting system work



## Application

Insulation Piercing Connector

## Dimensions

|                |           |
|----------------|-----------|
| Package Height | 0.000 in  |
| Package Weight | 0.000 lb. |
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |

## General

|                          |                     |
|--------------------------|---------------------|
| Application - For Use On | Copper and Aluminum |
| UPC                      | 621945653535        |

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)