



BIPC7502SC, IPC, Cu/Al, R: 250-500 (750 Tap), T: #2-4/0**

By Burndy
Catalog # [BIPC7502SC](#)

Mechanical Insulation Piercing Connector, Cu/Al, Splicing, Tapping, and Dead-End Applications. Run: 250-500 (**750 Tap), Tap: #2-4/0

Features

- Flexibility! One connector allows for tap, splice or dead-end configurations
- Time Savings! Requires no cable stripping, conductor brushing, inhibitor application or after installation taping
- Engineered shear bolt technology applies consistent torque for efficient and reliable connectors
- Easy installation and removal - only requires 6-point socket impact driver
- cULus Listed Splicing Wire Connector, AL9CU Rated, for copper and aluminum conductor combinations up to 90 degrees C, *600 Volt applications
- Insulation piercing design for use in multiple applications - overhead covered and bare taps, service and metering connections, and lighting system work



Application

Insulation Piercing Connector

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Application - For Use On UPC	Copper and Aluminum 621945653573
---------------------------------	-------------------------------------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)