



BISR1/0, Clear Insulated Splice Reducer, #14-1/0 AWG

By Burndy
Catalog # [BISR1/0](#)

Aluminum UNITAP In-Line Splice Reducer, Clear Insulation, #14-1/0 AWG, AL9CU



Features

- Type BISR In-Line Splice/Reducers are easily installed on code conductor
- UL486B Listed, Dual rated AL9CU for any stranded copper or stranded aluminum applications

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	14 AWG - 1/0 AWG
Conductor Size	14-1/0 AWG
Conductor Type	- AL C Str-Size - CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	In-Line

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	35 mm
Dimension - Height inch	1.38 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	74 mm
Dimension - Width mm	23 mm
Dimension - Width inch	0.91 in
Dimension - Length Overall inch	2.91 in

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Splice Reducer
UPC	781810134115
Type	BISR
Hex Key	3/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810134115
UPC 14 Digit GTIN	00781810134115

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)