

BITO4, Opp. Side, 2-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BITO4](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2 Sided Entry,
14-4 AWG, Al/Cu Rated, 1.16 IN L



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27.44 mm
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Dimension - Length Overall inch	1.08 in

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810134139
Type	BIT
Hex Key	1/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810134139
UPC 14 Digit GTIN	00781810134139

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	100

Operational

Temperature Rating	90°C
--------------------	------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)