




BS16, Vinyl Splice, #22-16 AWG

By Burndy
Catalog # BS16

Vinyl Splice For 22 - 16 AWG



Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion
- Expanded insulation support to lower inventory requirements
- Vinyl insulation provides an economical means of providing high dielectric values and cable insulation support

Application

For Accommodating A Broad Range Of 600 Volt Cables

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size Range	20 -16 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.145 in
Package Height	0.000 in
Dimension - Strip Length inch	1/4 in
Dimension - Length Overall inch	1.00 in
Dimension - Diameter Max Size inch	0.145 in

General

Insulation Type	Vinyl
Trade Name	VINYLINK™
Insulation	Y
Sub Brand	VINYLINK
Color Code	Red
Plated	Y
Type	BS
UPC 12 Digit	781810805169
UPC 14 Digit GTIN	00781810805169
Material	Copper
Plating Type	Tin
UPC	781810805169

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)