




BTCGC250, Mechanical Ground Clamp for Cable Tray

By Burndy
Catalog # [BTCGC250](#)

TRAY CLAMP 250 KCMIL - 6, Material Aluminum, Tin plated finish, Zinc-Plated Steel Screws



Features

- Tin plated aluminum for durable, long lasting corrosion resistance
- UL 467 Listed for Grounding and Bonding
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation, no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Zinc-Plated Screws, for Stainless Steel Screws use BTCGC250SS

Specifications

UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	250Kcmil - 6 AWG
Conductor - Copper Str Size Range	250Kcmil - 6 AWG

Dimensions

Height	2.43 in
Width	0.88 in
Package Height	0.000 in
Length	2.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	2.25 in x 0.88 in x 2.43 in

General

UPC	621945468818
-----	--------------

Logistics

Pallet Quantity	4800
Carton Quantity	75

Product Assets

[Catalog \[English\]](#)