



BDBMHC113502, 2-Pole Power Distribution Block

By Burndy
Catalog # [BDBMHC113502](#)

Distribution Block, High Conductive Al Body & Gas Filled Polycarbonate Insulator, 2 Poles, #6 AWG -350 kcmil (Run & Tap), 310 Amps



Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350
Number Of Poles	2
Conductor - AL Str Run Range	6-350
Conductor - AL Str Run	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0

	• 250 • 266.8 • 300 • 336.4 • 350
Conductor - AL Str Tap Range	6-350
Conductor - AL Str Tap	• 6 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	6-350
Conductor - Copper Str Tap	• 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350

Current

Amperage Rating	310 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Length	3.57 in
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.
Dimension - Width mm	91 mm
Dimension - Width inch	3.57 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Height	3.25 in
Width	3.88 in
Dimension - Length Overall inch	5.00 in
Dimensions	3.57 in x 3.88 in x 3.25 in

General

PlatedY



A Hubbell brand

Trade Name	VERSIPOLE™
UPC	781810645710
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810645710
UPC 14 Digit GTIN	00781810645710

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1014
Carton Quantity	9

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)