



CP3434, Heavy Duty Parallel Connector, Copper, A=500 kcmil, B=500 kcmil

By Burndy
Catalog # CP3434



Copper Alloy Heavy Duty Parallel Connector

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	500 kcmil
Conductor - Copper Str Size A	500 kcmil
Range	
Conductor - Copper Str Size B	500 kcmil
Range	

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	5 in
Dimension - Width fraction	2-1/2 in

General

Plated	N
UPC	781810012864
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810012864
UPC 14 Digit GTIN	00781810012864

Logistics

Minimum Pack Quantity	7
Pallet Quantity	1
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)