

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [CPR46A4](#)

Cable Spacer



Features

- Rigid spacer for large range of cables
- Designed for short spacing with more contact control
- One bolt design

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1200 kcmil • 1250 kcmil • 1272 kcmil • 1300 kcmil • 1351 kcmil • 1400 kcmil • 1431 kcmil • 1500 kcmil • 1590 kcmil • 1600 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - AL Str Size Range	1200 kcmil-1600 kcmil
Conductor - ACSR Str Size Range	1113 kcmil-1351.5 kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	75.9 mm
Length	4 in
Dimension - Height inch	2.73 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - B Length inch	2.13 in
Width	2.13 in
Dimension - Length Overall inch	5.97 in

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Plated	N
Material - Hardware	Aluminum
UPC	781810472538
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810472538
UPC 14 Digit GTIN	00781810472538

Logistics

Minimum Pack Quantity	1
Pallet Quantity	64
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)