



BDBMHCCOVER, Power Distribution Block Cover

By Burndy
Catalog # [BDBMHCCOVER](#)

Polycarbonate Cover for Medium Size BDBMH Style Power Distribution Blocks

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	---

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions



Dimension - Height mm	16.5 mm
Dimension - Height inch	0.65 in
Dimension - Width mm	44 mm
Dimension - Width inch	1.75 in
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.37 in

General

Plated	Y
Trade Name	VERSIPOLE™
UPC	781810646137
Insulation	Y
Material	Polycarbonate
Plating Type	Unplated
UPC 12 Digit	781810646137
UPC 14 Digit GTIN	00781810646137

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6600
Carton Quantity	200

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand