



CT250800RQ0, Cable Tie, 8" Max Bundle, UV Black, Releasable

By Burndy
Catalog # [CT250800RQ0](#)

Nylon UNIRAP™ Cable Tie - 250 Lb. Tensile Strength (Releasable), 25 pack

Features

- Releasable Cable Tie
- Specially suitable for prototype construction or temporary installation
- Also suitable where service often requires adding or subtracting wires from an existing bundle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	1.750 in
Length	29 in
Package Weight	1.070 lb.
Dimension - Width mm	13 mm
Dimension - Width inch	0.50 in
Package Length	34.500 in
Package Width	5.250 in
Dimension - L Length Overall mm	737 mm
Width	0.5 in
Dimension - Length Overall inch	29 in



Dimension - Bundle Diameter Max inch	8.00
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	250
---------------------------------------	-----

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810334874
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810334874

Logistics

Minimum Pack Quantity	25
Pallet Quantity	12000
Carton Quantity	1000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)