



CT50175M02, Tie, 1.87" Max Bundle, 50 Lb Tensile, UV Red

By Burndy
Catalog # [CT50175M02](#)

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features


- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Specifications

Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - UV Rated	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
Certification - CSA Approved	No
Military Spec Number	MS3367-1-2
Certification - 94V0 Rated	N

Dimensions

Package Height	4.250 in
Length	7.56 in
Package Weight	3.000 lb.
Dimension - Width mm	5 mm
Dimension - Width inch	0.18 in
Package Length	16.000 in
Package Width	12.000 in
Dimension - L Length Overall mm	192 mm
Width	0.18 in
Dimension - Length Overall inch	7.56 in



Dimension - Bundle Diameter Max inch	1.875
--------------------------------------	-------

Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Color	Red
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810338056
Material	Nylon 6/6
Military Specification	MS3367
UPC 14 Digit GTIN	00781810338056

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	10000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)