




# CTHS50700MCTHS50700M, Heat Stabilized, 1.87" Bundle, Black

By Burndy  
Catalog # [CTHS50700M](#)

Heat Stabilized Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength, 1.87" Max Bundle Dia, 7.56" Long



### Features

- Heat Stabilized Cable Tie

### Specifications

|                                    |     |
|------------------------------------|-----|
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |
| Certification - CSA Approved       | No  |

### Dimensions

|                                      |           |
|--------------------------------------|-----------|
| Package Height                       | 0.000 in  |
| Length                               | 7.56 in   |
| Package Weight                       | 0.000 lb. |
| Dimension - Width mm                 | 5 mm      |
| Dimension - Width inch               | 0.18 in   |
| Package Length                       | 0.000 in  |
| Package Width                        | 0.000 in  |
| Dimension - L Length Overall mm      | 192 mm    |
| Width                                | 0.18 in   |
| Dimension - Length Overall inch      | 7.56 in   |
| Dimension - Bundle Diameter Max inch | 1.88      |

### Force Related

|                                       |    |
|---------------------------------------|----|
| Rating - Minimum Tensile Strength lbs | 50 |
|---------------------------------------|----|

### General

|                   |                |
|-------------------|----------------|
| Color Code        | Black          |
| Series            | UNIRAP™ Series |
| UPC               | 781810661048   |
| Material          | Nylon 6/6      |
| UPC 12 Digit      | 781810661048   |
| UPC 14 Digit GTIN | 00781810661048 |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 1    |
| Carton Quantity       | 1000 |
| Packaging Type        | Bag  |

### Operational

|                                   |        |
|-----------------------------------|--------|
| Operating Temperature Celcius Max | 105 °C |
| Operating Temperature Celcius Min | -40 °C |

### Product Assets

[Catalog \[English\]](#)