



CUSA442TC38, 2-Hole Copper Stacking Adapter

By Burndy
Catalog # CUSA442TC38



Copper Stacking Adapter, Tin Plated, Suitable for Copper Terminals with 3/8" Stud, 1" Spacing, Rated up to 1000 kcmil

Features

- For use on terminals made from copper
- Designed specifically for stacking standard terminals, uses include placing the stacking adapter on the mounting plate and a terminal on top of the stack adapter and bolt down, or placing a stacking adapter on a terminal pad that will be mounted to a bus bar or mounting plate and a terminal on top of the stacking adapter, and bolt down
- May be used with standard NEMA two and four hole terminals, to stack four hole NEMA terminations requires use of two stacking adapters assembled side-by-side
- Stacking adapters are clearly marked

Application

Stacking Adapter

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	1000 KCMIL
Conductor - AL Str Size	1000 KCMIL
Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str	1000 KCMIL
Compact Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	10 AWG - 750 kcmil

Configuration

Connector Type	STACKING ADAPTER
----------------	------------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Height mm	38.1 mm
Dimension - Hole Size fraction	3/8
Dimension - Height inch	1.50 in
Dimension - L Length Overall mm	44 mm
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Width mm	28 mm
Dimension - Width inch	1.12 in
Dimension - Length Overall inch	1.75 in

General

Trade Name	HYSTACK™
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
UPC	781810249246
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810249246
UPC 14 Digit GTIN	00781810249246

Logistics

Minimum Pack Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)