



CUW44E, Copper Alloy Deadend Strain Clamp, 500-1000 kcmil

By Burndy
Catalog # [CUW44E](#)

Cast Cu Alloy Deadend Strain clamp, 500 - 1000 Kcmil Cu, Bright Dipped

Features

- High strength, two-bolt
- Single saddle design for short span distribution and strain bus application
- Galvanized steel clevis pin and U-bolts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	500 kcmil-1000 kcmil
Conductor - Copper Str Size	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions



Package Height	0.000 in
Dimension - Height mm	83.8 mm
Dimension - Height inch	3.3 in
Dimension - Height fraction	3-3/8 in
Dimension - B Length fraction	3-1/4 in
Package Weight	0.000 lb.
Dimension - Width mm	115 mm
Dimension - Width inch	4.53 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	222 mm
Dimension - B Length inch	3.25 in
Dimension - Width fraction	4-44/83 in
Dimension - Length Overall inch	8.75 in

General

Plated	Y
Material - Hardware	Galvanized Steel
UPC	781810091753
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 14 Digit GTIN	00781810091753

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)