



EP 1 HP Series Electric/Hydraulic Pump,
115/230V-AC, Use with all 10,000 psi
remote HYPRESS™ crimpers and cutters

By Burndy
Catalog # [EP101HP](#)

EP Series Pump, 1 HP 115V 60 Hz

Features

- Heavy duty design
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure
- 1 HP motor dual voltage/hertz

Application

Pumping

Specifications

Standards - RoHS Compliance CM
Status

Current

Current Draw Max 10 Amperes

Dimensions

Length 18.5 in
Width 11.75 in



Weight 72 lb.
Height 18.75 in
Dimensions 18.5 in x 11.75 in x 18.75 in

General

Application - For Use On Use with 10,000 psi Remote
Hydraulic Crimpers and Cutters
Pump
Type 781810033210
UPC 12 Digit 00781810033210
UPC 14 Digit GTIN
Tool Type Pump, Electric Hydraulic
UPC 781810033210

Logistics

Package Contents Pump only
Minimum Pack Quantity 1

Operational

- Power Source
- 1 HP 115/230V-AC
 - 60 Hz Motor

Product Assets

[Catalog \[English\]](#)