



EP 1/2 HP Series Electric/Hydraulic Pump,  
Use with all 10,000 psi remote HYPRESS™  
crimpers and cutters

By Burndy  
Catalog # [EP102](#)

EP Series Pump, 1/2 HP 220/230V 50/60 Hz

Features

- 1/2 HP motor
- Dual voltage/hertz
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure

Application

Pumping

Specifications

Standards - RoHS Compliance    CM  
Status

Current

Current Draw Max                      10 Amperes

Dimensions

Length                                      18.5 in  
Width                                        11.75 in



Weight                                      68 lb.  
Height                                      17.5 in  
Dimensions                                18.5 in x 11.75 in x 17.5 in

General

Application - For Use On                Use with 10,000 psi Remote  
Hydraulic Crimpers and Cutters  
Pump  
Type                                          781810033548  
UPC 12 Digit                                00781810033548  
UPC 14 Digit GTIN  
Tool Type                                    Pump, Electric Hydraulic  
UPC                                            781810033548

Logistics

Package Contents                        Pump only  
Minimum Pack Quantity                1

Operational

Power Source                              • 1/2 HP 220/230V-AC  
• 50/60 Hz Motor

Product Assets

[Catalog \[English\]](#)