



EP10 Pump with Foot Control, 10,000 psi

By Burndy
Catalog # [EP10FC](#)

EP Series Pump, EP10 with Quick Disc



Features

- Foot Control

Application

Pumping

Specifications

Standards - RoHS Compliance CM
Status

Current

Current Draw Max 10 Amperes

Dimensions

Length 18.5 in
Width 11.75 in
Weight 68 lb.
Height 17.5 in
Dimensions 18.5 in x 11.75 in x 17.5 in

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters Pump
Type	781810036556
UPC 12 Digit	00781810036556
UPC 14 Digit GTIN	Pump, Electric Hydraulic
Tool Type	781810036556
UPC	

Logistics

Package Contents	Pump, Foot Control
Minimum Pack Quantity	1

Operational

Power Source	• 1/2 HP 115/230V-AC • 60 Cycle • 1/2 HP @ 3450 RPM
--------------	---

Product Assets

[Catalog \[English\]](#)