



ES2R4WBOX, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES2R4WBOX](#)

BURNDY® INSULINK™ Service Entrance Sleeve

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1 STR, 2 STR
Conductor - Copper Str Size B	5 STR,6 STR,4 SOL
Conductor - AL Str Size A	1 STR, 2 STR
Conductor - AL Str Size B	5 STR,6 STR,4 SOL
Conductor - ACSR Str Size A	2 AWG
Conductor - ACSR Str Size B	6 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	70 mm
Dimension - Outside Diameter	.75 in
Dimension - Length Overall	2.75 in

General

Plated	Y
Insulation Type	Nylon
Die Index	BG
UPC	781810191781
Type	Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810191781
UPC 14 Digit GTIN	00781810191781

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11136
Carton Quantity	24

Product Assets

[Catalog \[English\]](#)